

# Quattroflow™ QF4400HT

QF4400HT SERIES  
Quaternary Diaphragm  
Pumps

## Integrated controller and high turn-down ratio

The new QF4400HT model is similar to the standard QF4400 pump, but has integrated the pump chamber, pump drive, motor and control box into one unit. The elimination of a separate control box results in a more compact design, a smaller footprint, and an easier handling.

The QF4400HT offers the following features and benefits:

- "All-in-One" technology; integration of pump chamber, pump drive, motor, controller and pump housing into one unit
- Extended turn-down ratio for a wider range of flow rates than the standard QF4400 model with optimal linearity
- High accuracy in controlling flow rates
- Compact design
- Keypad for manual control and display of motor speed
- Easy "Plug and Play" installation and startup with one power cable
- Three phase 400V power supply
- Available as Multiple-Use (pump chamber SS316L) and Single-Use (machined polypropylene)
- Clean-In-Place/Steaming-In-Place (CIP/SIP) and autoclavability for Multiple-Use models
- Autoclavability for Single-Use models
- Analog input (4-20mA) as standard
- Compatible with Quattroflow PID controller

Quattroflow™ has extended the HT product line of Quaternary (Four-Piston) Diaphragm Pumps with the new size QF4400HT. Whereas the existing QF1200HT pump size achieves a flow rate of 1,200 lph, the QF4400HT covers higher performance requirements with a flow rate of 5,000 lph.




*Quattroflow develops and manufactures, in close cooperation with its customers, specific Quaternary (Four-Piston) Diaphragm Pumps for critical applications in the pharmaceutical and biotech industries. The method of operation of Quattroflow pumps allows them to gently, safely and securely convey aqueous solutions and biological products that are sensitive to shear force. The four-piston design does not feature a mechanical shaft seal or wetted rotating parts, ensuring total product containment without abrasion or particle generation. Additionally, the four-piston pumping principle enables risk-free dry-running, low pulsation, self priming, and minimal particle generation.*

# Quattroflow™ QF4400HT

| Model Pump Type                                   | QF4400S-HT<br>Multiple-Use | QF4400SU-HT<br>Single-Use |
|---------------------------------------------------|----------------------------|---------------------------|
| <b>Flow Rate Maximum:</b>                         |                            |                           |
| Eccentric Shaft 6°                                | 5,000 lph (83 lpm)         | 5,000 lph (83 lpm)        |
| <b>Flow Rate Minimum:</b>                         |                            |                           |
| Eccentric Shaft 6°                                | 50 lph (0.83 lpm)          | 50 lph (0.83 lpm)         |
| <b>Pressure:</b>                                  |                            |                           |
| Temperature of Fluid < 40° C (104° F)             | 6 bar (87 psi)             | 4 bar (58 psi)            |
| Temperature of Fluid > 40° C (104° F)             | 4 bar (58 psi)             | 4 bar (58 psi)            |
| <b>Maximum Temperature:</b>                       |                            |                           |
| Fluid                                             | 80° C (176° F)             | 60° C (140° F)            |
| CIP                                               | 90° C (194° F)             | —                         |
| SIP                                               | 130° C (260° F)            | —                         |
| Autoclave                                         | 130° C (260° F)            | 130° C (260° F)           |
| <b>Pump Speed Range:</b>                          |                            |                           |
| rpm                                               | 10 - 1,200                 | 10 - 1,200                |
| <b>Suction Lift Dry at 1800 rpm:</b>              |                            |                           |
| Eccentric Shaft 6°                                | 4-4.5 m (13.1-14.7 ft)     | 4-4.5 m (13.1-14.7 ft)    |
| <b>Volume Specifications:</b>                     |                            |                           |
| Approximated Volume per Revolution at Free Output | 95 ml                      | 95 ml                     |
| Filling Volume Without Connectors                 | 820 ml                     | 820 ml                    |
| <b>Connection Specification (Standard):</b>       |                            |                           |
| Connectors                                        | 1 1/2" TC                  | 1 1/2" TC                 |
| Position of Connectors                            | Front                      | Front                     |

| Model Pump Type                               | QF4400S-HT<br>Multiple-Use                       | QF4400SU-HT<br>Single-Use                                           |
|-----------------------------------------------|--------------------------------------------------|---------------------------------------------------------------------|
| <b>Product Wetted Materials (Standard):</b>   |                                                  |                                                                     |
| Pump Chamber                                  | SS316L                                           | PP                                                                  |
| Valve Plate                                   | SS316L                                           | PP                                                                  |
| Diaphragms                                    | TPE                                              | TPE                                                                 |
| Valves                                        | EPDM / SS316L                                    | EPDM / SS316L                                                       |
| O-rings                                       | EPDM                                             | EPDM                                                                |
| <b>Certificates/Proofs (Optional):</b>        |                                                  |                                                                     |
| Elastomer (product wetted)                    | USP <88> Cl. VI;<br>FDA21CFR177;<br>BSE/TSE Safe | USP <88> Cl. VI;<br>FDA21CFR177;<br>BSE/TSE Safe;<br>USP 87/381/661 |
| Stainless Steel Parts (product wetted)        | 3.1; Surface Roughness;<br>Ferrite Content       | —                                                                   |
| <b>Motor:</b>                                 |                                                  |                                                                     |
| Maximum speed                                 | 1,200 min-1                                      | 1,200 min-1                                                         |
| Voltage                                       | 400 V                                            | 400 V                                                               |
| Power                                         | 4.0 kW                                           | 4.0 kW                                                              |
| <b>Pump Dimension with Motor and Housing:</b> |                                                  |                                                                     |
| Length                                        | 790 mm (31.10")                                  | 790 mm (31.10")                                                     |
| Width                                         | 275 mm (10.83")                                  | 275 mm (10.83")                                                     |
| Height                                        | 393 mm (15.47")                                  | 393 mm (15.47")                                                     |
| <b>Pump Weight with Motor and Housing:</b>    |                                                  |                                                                     |
|                                               | 90 kg (198 lb.)                                  | 75 kg (165 lb.)                                                     |



ALMATEC Maschinenbau GmbH  
Hochstraße 150-152  
47228 Duisburg, Germany  
Tel: +49 (2065) 89205-0 • Fax: +49 (2065) 89205-40  
info@almatec.de

Almatec reserves the right to modify the information and illustrations contained in this document without prior notice. This is a non-contractual document. 10-2018.

Authorized PSG® Partner: